

NexiusZoom (EVO)

HIGHLIGHTS

- Binocular and trinocular heads with HWF 10x/22 mm (NexiusZoom) or HWF 10x/23 mm eyepieces (NexiusZoom EVO)
- Standard magnifications from 6.7 to 45x or 6.5 to 55x (EVO)
- Magnifications up to 180x or 220x (EVO) with auxiliary lenses
- · Ergonomically designed stands
- · Double 3 W LED illumination
- · Large working distance
- 10 years warranty



EYEPIECES

The standard NexiusZoom is supplied with a pair of HWF 10x/22 mm eyepieces.

The NexiusZoom EVO is supplied with a pair of HWF 10x/23 mm eyepieces

HEAD

Binocular or trinocular heads with 45° inclined tubes. Both eyepieces with \pm 5 diopter adjustments. Interpupillary distance adjustable between 54 mm and 75 mm

OBJECTIVES

The standard NexiusZoom is supplied with a 1:6.7 zoom objective with 0.67x to 4.5x magnifications, a field of view from 33 mm to 4.9 mm. Working distance 110 mm. Auxiliary lenses 0.5x, 0.75x, 1.5x and 2.0x available.

The NexiusZoom EVO is supplied with a 1:8.4 zoom objective with 0.65x to 5.5x magnifications, a field of view from 35.4 mm to 4.2 mm. Working distance 110 mm. Auxiliary lenses 0.5x, 0.75x, 1.5x and 2.0x available.

All optics are anti-fungus treated and anti-reflection coated for maximum light throughput

STAND

Ergonomically designed pillar or rack & pinion stand with LED illumination and 2 object clamps. Ergonomically designed universal or boom stands, without illumination. Articulated arm stand for table mounting, without

illumination. Alloy metal cast, hardened off-white painted



STAGE

NEW: 180 x 155mm X-Y mechanical stage with 76 x 55mm translation stage and transparent glass plate for NexiusZoom, fixed on stage of microscope. Only available with new microscopes (due to fixing), so it has to be ordered with the purchase of a microscope (See picture: NZ.9505)

ILLUMINATION

The 3 W transmitted and incident LED illuminators with internal power supply 100-240 V operation. Both illuminators can be used simultaneously and the light intensities can be adjusted separately

PACKAGING

 $Supplied\ with\ power\ cord,\ dust\ cover,\ a\ spare\ fuse,\ user\ manual.\ All\ packed\ in\ a\ polystyrene\ box$





NZ.5302 / NZ.5303



NexiusZoom EVO NZ.5313



MODELS NEXIUSZOOM 0.67-4.5 (WF10X/22MM)

	Binocular	Trinocular	Pillar stand	Rack & pinion stand	Universal stand	Boom stand	Articulated arm stand	Weight(kg)
NZ.1902-P	•							5.0
NZ.1902-S	•			•				4.9
NZ.1902-U	•				•			15.6
NZ.1902-B	•					•		22.1
NZ.1902-A	•						•	8.6
NZ.1903-P		•	•					5.2
NZ.1903-S		•		•				5.1
NZ.1903-U		•			•			15.7
NZ.1903-B		•				•		22.2
NZ.1903-A							•	8.7

MODELS NEXIUSZOOM EVO 0.65-5.5 (WF10X/23MM)

	Binocular	Trinocular	Pillar stand	Rack & pinion stand	Universal stand	Boom stand	Articulated arm stand	Weight (kg)
NZ.1702-P	•							5.0
NZ.1702-S	•			•				4.9
NZ.1702-U	•				•			15.6
NZ.1702-B	•					•		22.1
NZ.1702-A	•						•	8.6
NZ.1703-P		•	•					5.2
NZ.1703-S		•		•				5.1
NZ.1703-U		•			•			15.7
NZ.1703-B		•				•		22.2
NZ.1703-A							•	8.7

MAGNIFICATIONS

 $\textbf{NexiusZoom standard} \ \text{Working distance and field of view with standard HWF 10x/22 High Wide Field eyepieces}$

Zoom indication	Objective 1x Working dista	-	Auxiliary Working dista		Auxiliary l Working dista		Auxiliary Working dist		Auxiliary Working dist	
	Total Magnifications	Field of view in mm	Total Magnifications	Field of view in mm	Total Magnifications	Field of view in mm	Total Magnifications	Field of view in mm	Total Magnifications	Field of view in mm
0.67	6.7	32.8	3.35	65.7	5.0	43.8	10.1	21.9	13.4	16.4
0.7	7.0	31.4	3.5	62.9	5.3	41.9	10.5	21.0	14.0	15.7
0.8	8.0	27.5	4.0	55.0	6.0	36.7	12.0	18.3	16.0	13.8
1.0	10.0	22.0	5.0	44.0	7.5	29.3	15.0	14.7	20.0	11.0
1.5	15.0	14.7	7.5	29.3	11.3	19.6	22.5	9.8	30.0	7.3
2.0	20.0	11.0	10.0	22.0	15.0	14.7	30.0	7.3	40.0	5.5
3.0	30.0	7.3	15.0	14.7	22.5	9.8	45.0	4.9	60.0	3.7
4.0	40.0	5.5	20.0	11.0	30.0	7.3	60.0	3.7	80.0	2.8
4.5	45.0	4.9	22.5	9.8	33.8	6.5	67.5	3.3	90.0	2.4

NexiusZoom EVO Working distance and field of view with standard HWF 10x / 23 High Wide Field eyepieces

Zoom indication	Objective 1x Working dista		Auxiliary Working dista		Auxiliary l Working dista		Auxiliary Working dist		Auxiliary Working dist	
	Total Magnifications	Field of view in mm	Total Magnifications	Field of view in mm	Total Magnifications	Field of view in mm	Total Magnifications	Field of view in mm	Total Magnifications	Field of view in mm
0.65	6.5	35.4	3.25	70.8	4.9	47.2	9.8	23.6	13.0	17.7
0.7	7.0	32.9	3.5	65.7	5.3	43.4	10.5	21.9	14.0	16.4
0.8	8.0	28.8	4.0	57.5	6.0	38.3	12.0	19.2	16.0	14.4
1.0	10.0	23.0	5.0	46.0	7.5	30.7	15.0	15.3	20.0	11.5
1.5	15.0	15.3	7.5	30.7	11.3	20.4	22.5	10.2	30.0	7.7
2.0	20.0	11.5	10.0	23.0	15.0	15.3	30.0	7.7	40.0	5.8
3.0	30.0	7.7	15.0	15.3	22.5	10.2	45.0	5.1	60.0	3.8
4.0	40.0	5.8	20.0	11.5	30.0	7.7	60.0	3.8	80.0	29
4.5	45.0	5.1	22.5	10.2	33.8	6.8	67.5	3.4	90.0	2.6
5.5	55.0	4.2	27.5	8.4	41.3	5.6	82.5	2.8	110	2.1









ESD SAFE MODELS

	Binocular	Trinocular	Pillar stand	Rack & pinion stand	Universal stand	Boom stand	Articulated arm stand	Antistatic ESD	Weight (kg)
NZ.1902-P-ESD	•		•						5.0
NZ.1902-S-ESD	•			•					4.9
NZ.1902-U-ESD	•							•	15.6
NZ.1902-B-ESD	•					•		•	22.1
NZ.1903-P-ESD		•	•					•	5.3
NZ.1903-S-ESD		•		•					5.1
NZ.1903-U-ESD		•			•			•	15.7
NZ.1903-B-ESD		•				•		•	22.2



DIMENSIONS







ACCESSORIES AND SPARE PARTS

NZ.5302	NexiusZoom binocular head with eyepieces
	NexiusZoom trinocular head with eyepieces
	NexiusZoom EVO binocular head with eyepieces
	NexiusZoom EVO trinocular head with eyepieces
	, ,
NZ.6010	Pair of HWF 10x / 22 mm eyepieces
NZ.6015	Pair of HWF 15x / 16 mm eyepieces
NZ.6020	Pair of HWF 20x / 12 mm eyepieces
NZ.6110	HWF 10x / 22 mm eyepiece with micrometer
NZ.6210	Pair of HWF 10x / 23 mm eyepieces (only suitable for the EVO)
NZ.6099	Pair of eyecups
NZ.8903	Auxiliary lens 0.3x (not suitable for NZ.1902-5, NZ.1903-5, NZ.1902-
	S-ESD and NZ.1903-S-ESD)
NZ.8905	Auxiliary lens 0.5x. Working distance 165 mm (not suitable for
N7 0007	NZ.1902-5 and NZ.1903-5)
	Auxiliary lens 0.75x. Working distance 120 mm
	Auxiliary lens 1.5x. Working distance 45 mm Auxiliary lens 2.0x. Working distance 30 mm (not suitable for
NZ.0920	NZ.1902-S and NZ.1903-S)
NZ.8950	Protection glass for NexiusZoom head
	· · · · · · · · · · · · · · · · · · ·
NZ.9010	Ergonomic rack & pinion stand with transmitted and incident LED
NZ.9010	Ergonomic rack & pinion stand with transmitted and incident LED illuminators
	illuminators
NZ.9015	illuminators Ergonomic pillar stand with transmitted and incident LED
NZ.9015 NZ.9020	illuminators Ergonomic pillar stand with transmitted and incident LED illuminators
NZ.9015 NZ.9020 NZ.9030	illuminators Ergonomic pillar stand with transmitted and incident LED illuminators Universal (single arm) stand without NexiusZoom head holder
NZ.9015 NZ.9020 NZ.9030 NZ.9090	illuminators Ergonomic pillar stand with transmitted and incident LED illuminators Universal (single arm) stand without NexiusZoom head holder Boom (double arm) stand without NexiusZoom head holder
NZ.9015 NZ.9020 NZ.9030 NZ.9090 NZ.9025	illuminators Ergonomic pillar stand with transmitted and incident LED illuminators Universal (single arm) stand without NexiusZoom head holder Boom (double arm) stand without NexiusZoom head holder NexiusZoom head holder (for NZ.9020 and NZ. 9030) Articulated arm stand with table clamp (without NexiusZoom head holder)
NZ.9015 NZ.9020 NZ.9030 NZ.9090 NZ.9025	illuminators Ergonomic pillar stand with transmitted and incident LED illuminators Universal (single arm) stand without NexiusZoom head holder Boom (double arm) stand without NexiusZoom head holder NexiusZoom head holder (for NZ.9020 and NZ. 9030) Articulated arm stand with table clamp
NZ.9015 NZ.9020 NZ.9030 NZ.9090 NZ.9025 NZ.9081	illuminators Ergonomic pillar stand with transmitted and incident LED illuminators Universal (single arm) stand without NexiusZoom head holder Boom (double arm) stand without NexiusZoom head holder NexiusZoom head holder (for NZ.9020 and NZ. 9030) Articulated arm stand with table clamp (without NexiusZoom head holder) NexiusZoom head holder (for articulated arm stand NZ.9025)
NZ.9015 NZ.9020 NZ.9030 NZ.9090 NZ.9025 NZ.9081	illuminators Ergonomic pillar stand with transmitted and incident LED illuminators Universal (single arm) stand without NexiusZoom head holder Boom (double arm) stand without NexiusZoom head holder NexiusZoom head holder (for NZ.9020 and NZ. 9030) Articulated arm stand with table clamp (without NexiusZoom head holder) NexiusZoom head holder (for articulated arm stand NZ.9025) Polarization kit for NexiusZoom: 360° rotatable round stage with
NZ.9015 NZ.9020 NZ.9030 NZ.9090 NZ.9025 NZ.9081	illuminators Ergonomic pillar stand with transmitted and incident LED illuminators Universal (single arm) stand without NexiusZoom head holder Boom (double arm) stand without NexiusZoom head holder NexiusZoom head holder (for NZ.9020 and NZ. 9030) Articulated arm stand with table clamp (without NexiusZoom head holder) NexiusZoom head holder (for articulated arm stand NZ.9025) Polarization kit for NexiusZoom: 360° rotatable round stage with built-in polarization filter (NZ.9524) + analyzer in mount to be
NZ.9015 NZ.9020 NZ.9030 NZ.9090 NZ.9025 NZ.9081 NZ.9520	illuminators Ergonomic pillar stand with transmitted and incident LED illuminators Universal (single arm) stand without NexiusZoom head holder Boom (double arm) stand without NexiusZoom head holder NexiusZoom head holder (for NZ.9020 and NZ. 9030) Articulated arm stand with table clamp (without NexiusZoom head holder) NexiusZoom head holder (for articulated arm stand NZ.9025) Polarization kit for NexiusZoom: 360° rotatable round stage with built-in polarization filter (NZ.9524) + analyzer in mount to be screwed under head (NZ.9525)
NZ.9015 NZ.9020 NZ.9030 NZ.9090 NZ.9025 NZ.9081 NZ.9520	illuminators Ergonomic pillar stand with transmitted and incident LED illuminators Universal (single arm) stand without NexiusZoom head holder Boom (double arm) stand without NexiusZoom head holder NexiusZoom head holder (for NZ.9020 and NZ. 9030) Articulated arm stand with table clamp (without NexiusZoom head holder) NexiusZoom head holder (for articulated arm stand NZ.9025) Polarization kit for NexiusZoom: 360° rotatable round stage with built-in polarization filter (NZ.9524) + analyzer in mount to be screwed under head (NZ.9525) 360° rotatable round stage with built-in polarization filter for
NZ.9015 NZ.9020 NZ.9030 NZ.9090 NZ.9025 NZ.9081 NZ.9520	illuminators Ergonomic pillar stand with transmitted and incident LED illuminators Universal (single arm) stand without NexiusZoom head holder Boom (double arm) stand without NexiusZoom head holder NexiusZoom head holder (for NZ.9020 and NZ. 9030) Articulated arm stand with table clamp (without NexiusZoom head holder) NexiusZoom head holder (for articulated arm stand NZ.9025) Polarization kit for NexiusZoom: 360° rotatable round stage with built-in polarization filter (NZ.9524) + analyzer in mount to be screwed under head (NZ.9525) 360° rotatable round stage with built-in polarization filter for NexiusZoom
NZ.9015 NZ.9020 NZ.9030 NZ.9090 NZ.9025 NZ.9081 NZ.9520	illuminators Ergonomic pillar stand with transmitted and incident LED illuminators Universal (single arm) stand without NexiusZoom head holder Boom (double arm) stand without NexiusZoom head holder NexiusZoom head holder (for NZ.9020 and NZ. 9030) Articulated arm stand with table clamp (without NexiusZoom head holder) NexiusZoom head holder (for articulated arm stand NZ.9025) Polarization kit for NexiusZoom: 360° rotatable round stage with built-in polarization filter (NZ.9524) + analyzer in mount to be screwed under head (NZ.9525) 360° rotatable round stage with built-in polarization filter for
NZ.9015 NZ.9020 NZ.9030 NZ.9090 NZ.9025 NZ.9081 NZ.9520 NZ.9524	illuminators Ergonomic pillar stand with transmitted and incident LED illuminators Universal (single arm) stand without NexiusZoom head holder Boom (double arm) stand without NexiusZoom head holder NexiusZoom head holder (for NZ.9020 and NZ. 9030) Articulated arm stand with table clamp (without NexiusZoom head holder) NexiusZoom head holder (for articulated arm stand NZ.9025) Polarization kit for NexiusZoom: 360° rotatable round stage with built-in polarization filter (NZ.9524) + analyzer in mount to be screwed under head (NZ.9525) 360° rotatable round stage with built-in polarization filter for NexiusZoom 360° rotatable analyser in mount to be screwed under head of
NZ.9015 NZ.9020 NZ.9030 NZ.9090 NZ.9025 NZ.9081 NZ.9520 NZ.9524 NZ.9525 AE.5168-	illuminators Ergonomic pillar stand with transmitted and incident LED illuminators Universal (single arm) stand without NexiusZoom head holder Boom (double arm) stand without NexiusZoom head holder NexiusZoom head holder (for NZ.9020 and NZ. 9030) Articulated arm stand with table clamp (without NexiusZoom head holder) NexiusZoom head holder (for articulated arm stand NZ.9025) Polarization kit for NexiusZoom: 360° rotatable round stage with built-in polarization filter (NZ.9524) + analyzer in mount to be screwed under head (NZ.9525) 360° rotatable round stage with built-in polarization filter for NexiusZoom 360° rotatable analyser in mount to be screwed under head of NexiusZoom
NZ.9015 NZ.9020 NZ.9030 NZ.9090 NZ.9025 NZ.9081 NZ.9520 NZ.9524 NZ.9525 AE.5168- NZ.9950	illuminators Ergonomic pillar stand with transmitted and incident LED illuminators Universal (single arm) stand without NexiusZoom head holder Boom (double arm) stand without NexiusZoom head holder NexiusZoom head holder (for NZ.9020 and NZ. 9030) Articulated arm stand with table clamp (without NexiusZoom head holder) NexiusZoom head holder (for articulated arm stand NZ.9025) Polarization kit for NexiusZoom: 360° rotatable round stage with built-in polarization filter (NZ.9524) + analyzer in mount to be screwed under head (NZ.9525) 360° rotatable round stage with built-in polarization filter for NexiusZoom 360° rotatable analyser in mount to be screwed under head of NexiusZoom WZ Heating stage with PID controller up to 50oC

NZ.9833 C-mount adapter with 0.33x lens for 1/3" cameras (suitable for trinocular models) NZ.9850 C-mount adapter with 0.5x lens for 1/2" cameras (suitable for trinocular models) 50.876 Dark field attachment AE.5130 Universal SLR camera adapter with 2x projection lens for 23.2 mm tubes. Need T2 adapter AE.5020 T2 adapter for Nikon D digital SLR cameras AE.5040 T2 adapter for Canon EOS digital SLR camerasOther T2 adapters **LE.1974** Ring illuminator with 72 LEDs with adjustable light intensity. External mains adapter 100-240 V. With segment controller. Brightness of 21.000 Lux at height of 100 mm and color temperature of 6.500K. Mounting diameter between 25-61 mm **LE.1973** Ring illuminator with 144 LEDs with adjustable light intensity. External mains adapter 100-240 V. With segment controller. Brightness of 23.000 Lux at height of 100 mm and color temperature of 6.500K. Mounting diameter between 25-61 mm

AE.1112 Object micrometer 50 mm (divided in 500 parts on glass slide

76 x 26 mm)



NZ.9572 Adjustable GEM object clamp for NexiusZoom (EVO)